CIL EMU CRITICAL ITEMS LIST

5/30/2002 SUPERSEDES 12/31/2001

Page 1

Date: 4/24/2002

NAME P/N		FAILURE MODE &		
QTY	CRIT	CAUSES	FAILURE EFFECT	RATIONALE FOR ACCEPTANCE
	· ·	106FM19		
ADJUSTABLE THERMAL MITTEN ASSEMBLY ITEM 106 (1) LEFT (1) RIGHT 0106-811540-03/04 (2)	2/2	Loss of adjustable thermal mitten assembly. Defective thread material. Retention strap separated from mitten; loose Velcro.	END ITEM: Adjustable thermal mitten damaged or loose from glove. GFE INTERFACE: Local heating or cooling of glove when grasping hot or cold objects, and local cooling when grasping cold objects. MISSION: Terminate EVA. CREW/VEHICLE: None. TIME TO EFFECT /ACTIONS: Seconds. TIME AVAILABLE: N/A TIME REQUIRED: N/A REDUNDANCY SCREENS: A-N/A B-N/A C-N/A	 A. Design - The Adjustable Thermal Mitten Assembly is designed to provide additional thermal protection beyond that provided by the glove TMG. The assembly utilizes Fiberglass felt on the palmer surfaces of the mitten as an insultive material. The felt is sandwiched between two layers of Reinforced Aluminized Maylar on either side of the felt. This insulative ply-up is encased between nomex fabric externally and teflon fabric internally. Thermal protection for the back side of the hand is provided by utilizing four layers of Reinforced Aluminized Maylar; two layers with the face side positioned inward to the hand; two layers with the face side positioned outward from the hand. This insulative ply-up in encased between two layers of teflon fabric. The Adjustable Thermal Mitten Assembly is secured to the Glove Assembly by use of velcro adjustments straps at the wrist location and adjustment cords (Gortex) which are routed through the back of the assembly. All stitching is performed using a 301 stitch, 8-10 psi per federal standard 751, using nomex "E" thread. Thread ends are secured with a surgeons knot which is coated with urethane adhesive. The nomex fabric has a tensile strength of 225 lbs. in the Warp direction and 170 lbs. in the Fill direction. The teflon fabric has a tensile strength of 47 lbs/in in the Warp direction and 40 lbs/in in the Fill direction. B. Test - Certification - Material manufactured to ILC requirements at an approved supplier are documented from procurement through shipping by the supplier. ILC incoming receiving inspection verifies that the materials received are as identified in the procurement documents, that no damage has cocurred during shipment and that appropriate data have been received which provide traceability information. The following MIP's are performed during the glove assembly manufacturing process to assure that the failure causes are preclued from the fabricated item: 1. Visual Inspection to verify materials

CIL EMU CRITICAL ITEMS LIST			5/30/2002 SU	Page 2 Date: 4/24/2002	
NAME P/N QTY	CRIT	FAILURE MODE & CAUSES	FAILURE EFFECT	RATIONALE FOR ACCEPTANCE	
		106FM19			
				No training specifically covers this failure mode. Operational Considerations - None.	

_ _ _ _ _ _ _ _ _

_ __ __ __

EXTRAVEHICULAR MOBILITY UNIT

SYSTEMS SAFETY REVIEW PANEL REVIEW

FOR THE

I-106 GLOVE ASSEMBLY

CRITICAL ITEM LIST (CIL)

EMU CONTRACT NO. NAS 9-97150

Prepared by: __________ Project Engineering

Approved by:

<u>M. Snydin</u> HS - Reliability

R. Munford 4/24/02 HS - Engineering Manager

Janw 5/23/02

Che Jon 6/3/02

6/05/02 ASA CION -

;/3/02 Riceran